

3M Food Safety

3M™ Sample Collection Products



# Experience confidence

The complete 3M sample handling system

## Collect.

Better testing begins with better samples — and better samples are obtained when you use the best collection tools. 3M™ Sample Collection solutions provide quality products designed specifically for microbial surface sampling. Make environmental testing and product sampling easy and convenient with the full line of 3M Sample Collection products.

- Easy to use for product sampling and environmental testing
- Exceptional convenience and quality
- Increased productivity and efficiency
- Reliable and accurate — time after time
- Improved consistency from technician to technician and plant to plant



# Collect.

Sponges and swabs designed specifically for microbial surface sampling.

## 3M™ Sponge-Sticks\*

- Allows sampling without the need to directly handle the sponge, increasing operator efficiency with less risk of contamination
- Easier to reach ceilings, into drains and pipes, and around equipment
- Sturdy sponge snaps free from plastic handle after sampling
- Biocide-free cellulose sponge maintains *Listeria* organism viability within 72 hours of refrigeration\*\*
- Available in dry or pre-hydrated formats, with or without irradiated gloves



## 3M™ Hydrated Sponges

- Ready-to-use, pre-hydrated sponges for easy and convenient sample collection
- Available in a variety of pre-hydrated dilutions
- Biocide-free cellulose sponge maintains *Listeria* organism viability within 72 hours of refrigeration\*\*
- Durable sponge withstands scrubbing
- Sponge bag with write-on label
- Available with or without irradiated gloves



## 3M™ Dry-Sponges

- Dry sponge in a sample bag
- Ideal for those who prefer to use their own sampling broths or a broth not available with the 3M™ Hydrated Sponges
- Durable sponge made from biocide-free cellulose to help maintain organism viability



## 3M™ Extendable Poles

- Designed for use with the 3M™ Sponge Stick for easier sampling of remote and hard-to-reach areas
- Lightweight, sturdy aluminum construction
- Minimizes bending and stretching of plant personnel
- Safely sample ceilings and tanks



\*Formerly known as Spongesicle.

\*\*Technical data summary can be provided upon request.

Catalog No.	Description	Qty.
<b>3M™ Sponge-Sticks</b>		
SSL100	3M™ Sponge-Stick, 1.5" x 3" Sponge, dry, 30 oz. bag	100
SSL10BPW	3M™ Sponge-Stick, 1.5" x 3" Sponge w/10mL Buffered Peptone Water Broth, 30 oz. bag, 5 bags of 20	100
SSL10LET	3M™ Sponge-Stick, 1.5" x 3" Sponge w/10mL Letheen Broth, 5 bags of 20	100
SSL10LET2G	3M™ Sponge-Stick, 1.5" x 3" Sponge w/10mL Letheen Broth, 30 oz. bag, 2 gloves, 5 bags of 20	100
SSL10DE	3M™ Sponge-Stick, 1.5" x 3" Sponge w/10mL D/E Neutralizing Broth, 30 oz. bag, 5 bags of 20	100
SSL10NB	3M™ Sponge-Stick, 1.5" x 3" Sponge w/10mL Neutralizing Buffer, 30 oz. bag, 5 bags of 20	100
SSL10NB2G	3M™ Sponge-Stick, 1.5" x 3" Sponge w/10mL Neutralizing Buffer, 30 oz. bag, 2 gloves, 5 bags of 20	100

### 3M™ Hydrated Sponges

HS10BPW	3M™ Hydrated Sponge, 1.5" x 3" Sponge w/10mL Buffered Peptone Water Broth, 5 bags of 20	100
HS10BPW2G	3M™ Hydrated Sponge, 1.5" x 3" Sponge w/10mL Buffered Peptone Water Broth, 2 gloves, 5 bags of 20	100
HS10DE2G	3M™ Hydrated Sponge, 1.5" x 3" Sponge w/10mL D/E Neutralizing Buffer, 2 gloves	100
HS10LET	3M™ Hydrated Sponge, 1.5" x 3" Sponge w/10mL Letheen Broth, 5 bags of 20	100
HS10LET2G	3M™ Hydrated Sponge, 1.5" x 3" Sponge w/10mL Letheen Broth, 2 gloves, 5 bags of 20	100
HS119510NB	3M™ Hydrated Sponge, 1.5" x 3" Sponge w/10mL Neutralizing Buffer, 50 oz. bag	100
HS10NB	3M™ Hydrated Sponge, 1.5" x 3" Sponge w/10mL Neutralizing Buffer, 5 bags of 20	100
HS10NB2G	3M™ Hydrated Sponge, 1.5" x 3" Sponge w/10mL Neutralizing Buffer, 2 gloves, 5 bags of 20	100
HS2410NB2G	3M™ Hydrated Sponge, 1.5" x 3" Sponge w/10mL Neutralizing Buffer, 24 oz. bag, 2 gloves	100

### 3M™ Dry-Sponges

BP135DS	3M™ Dry-Sponge w/4" String, 1.5" x 3" Sponge, 18 oz. bag	100
BP133ES	3M™ Dry-Sponge, 18 oz. printed bag	100
BP237SPG	3M™ Dry-Sponge, Sponge w/glove, 18 oz. bag	100

### 3M™ Extendable Poles

XSLSSL10NB	3M™ Extendable Pole Kit, (1) XSL-008 and (1) SSL-10NB	1
XSL008	3M™ Extendable Pole w/Sponge Holder, 8 ft.	1



### 3M™ Quick Swabs

- Ready-to-use environmental swab quickly delivers 1mL of sample onto a 3M™ Petrifilm™ Plate
- Increased accuracy
- Improved consistency from technician to technician and plant to plant
- Labor savings in dilution mixing and pipetting
- Better productivity and efficiency
- Can be used wet or dry



### 3M™ Swab-Samplers

- Ideal for sampling hard-to-reach areas with long, pre-hydrated 9cm swab
- Premeasured fill volumes allow for qualitative or quantitative use
- Blue stick is easy to detect if dropped onto production area or floor
- Can stand alone or fit into a standard test tube rack
- Ample headspace for effective vortexing

### 3M™ Enviro Swabs

- Designed to minimize the risk of sample contamination and improve the detection of bacteria on all types of surfaces
- Large swab head with shaped tip to sample crevices for efficient collection
- Flexible plastic stem allows swabbing of difficult-to-access areas
- Free of substances that inhibit bacteria
- Specially formatted transport medium
- Easily re-sealed for transport



Catalog No.	Description	Qty.
<b>3M™ Quick Swabs</b>		
6432	3M™ Quick Swab	50
6433	3M™ Quick Swab	250

<b>3M™ Swab-Samplers</b>		
RS96010BPW	3M™ Swab-Sampler w/10mL Buffered Peptone Water Broth	100
RS96010DE	3M™ Swab-Sampler w/10mL D/E Neutralizing Broth	100
RS9601LET	3M™ Swab-Sampler w/1mL Letheen Broth	100
RS9604LET	3M™ Swab-Sampler w/4mL Letheen Broth	100
RS9605LET	3M™ Swab-Sampler w/5mL Letheen Broth	100
RS96010LET	3M™ Swab-Sampler w/10mL Letheen Broth	100
RS9604NB	3M™ Swab-Sampler w/4mL Neutralizing Buffer	100
RS96010NB	3M™ Swab-Sampler w/10mL Neutralizing Buffer	100

<b>3M™ Enviro Swabs</b>		
ENVSWB25	3M™ Enviro Swab	25
ENVSWB25D	3M™ Enviro Swab, Dry	25





