

20-gallon Foam unit

FI-20N



the good stuff

- **easy to use, easy to maintain**
designed for portability, efficiency, and hassle-free maintenance. Our quick-change pump and tool-free, hinged access plate reduce downtime when a repair is needed.
- **natural tank**
see chemical volume levels at a glance.
- **configure with color**
lids and hoses come in a variety of colors to match your chemical management systems and quickly tell units apart in your chemical cage.

Features

- draws from pre-mixed solution
- powered by compressed air
- hinged back plate provides tool-free access to components
- quick-change pump
- natural color tank for easy visibility of product levels
- integrated hose wraps
- in-line strainer to protect pump from debris
- anti-kink hose protection
- front-facing drain
- hinged lid

options

- color coding
 - Lid – 7 colors (BK, BL, GN, YL, RD, PL, OR)
 - Discharge hose – 4 colors (BL, GN, YL, RD)

industries

- institutional
- food and beverage
- manufacturing
- aviation
- agriculture
- remediation



how to buy



800 567 5420 | sales@foamit.com

specs

- power typecompressed air
- chemical pickup type.....draws from pre-mixed solution
- number of products unit can draw fromone product
- suction line length/diameter 3/8 in. (9.5 mm) inside diameter
- capacity 20 gallons (75.71 liters)
- discharge line length/diameter:.....30 ft. (9 m) hose,
with 3/4 in. (19 mm) inside diameter
- discharge wand/tip type7 in. (17.8 cm) stainless steel wand
with zero tip and ball valve
- output distance.....25-30 ft. (7-9 m)
- output volume20-45 gal/min (75-170 l/min) of foam
- flow rate2 gal/min (7.6 l/min)
- pump seals Santoprene, Viton, or Kalrez
- wheel type: two 10 inch non-marking wheels,

requirements

- compressed air requirements.....40-80 psi (3-5 bar)
with 5-8 cfm (141-227 l/min)
- liquid temperature range.....40-100 ° F (4.4-37 ° C)
- chemical compatibility.....chemical products
used with this equipment must be formulated for this type
of application and compatible with unit materials and pump
seals. For more information on chemical compatibility,
consult the manufacturer or SDS for your product or contact
our customer service department.

Distributed by:

NELSON JAMESON
INC.

800-826-8302 nelsonjameson.com