



Since the measurement range of PAL-2 is Brix 45.0 - 93.0%, it can measure various high concentration samples such as jam, marmalade, jelly, honey and concentrated juice. The International Protection class of PAL-2 is IP65, so it can clean thick samples under running water. If you measure boiling jam or marmalade, we recommend [PAL-H](#)

Specifications

Model	PAL-2
Cat.No.	3820
Range	Brix : 45.0 to 93.0 %
Accuracy	±0.2 %
Temperature compensation	10 to 100° C

Options

- MAGIC™ (for PAL) : RE-39411
 - STRAP : RE-39410
 - PAL-CASE : RE-39409
 - PAL Silicone Cover : RE-39413
 - 50% Sucrose ($\pm 0.05\%$) : RE-110050
 - 60% Sucrose ($\pm 0.05\%$) : RE-110060
- * Calibration Certificate : Contact an ATAGO representative for details.

Patent for Invention Registration No. ZL200310103015.2 (China)

Patent for Design Registration No. ZL03303431.1 (China), 089244 (Taiwan)

Patent Granted in countries around the world.