

## CORIO C Heating Immersion Circulator

### The new generation of laboratory circulators

The CORIO™ C Immersion Circulator is the basic model of the CORIO™ circulator portfolio. The bath attachment clamp is included in delivery and facilitates mounting of the circulator on any bath tank up to 30 liters.

### Your advantages

- Precise temperature control
- For internal standard applications
- For bath tanks with a max. filling volume of 30 liters
- Bright, white, easy to read display
- Very quiet
- Easy operation
- Class I (NFL) according to DIN 12876-1



### Technical Data

Order No.	9011000
Model series	CORIO
Category	Heating Immersion Circulators
Working temperature range (°C)	+20 ... +100
Temperature stability (°C)	±0.03
Setting / display resolution	0.1 °C
Temperature Display	LED
Heating capacity (kW)	2
Circulation capacity Flow rate (l/min)	6
Circulation capacity Pressure (bar)	0.1
Ambient temperature	5...40 °C
Dimensions W x L x H (cm)	13.2 x 16 x 36.2
Weight (kg)	1.9
Cooling coil	optional
Usable immersion depth (cm)	16.6
Available voltage versions	208 - 230 V / 50-60 Hz 100 - 115 V / 50-60 Hz

## Characteristics



### 100% Checked.

100% testing. 100% quality. Each CORIO™ undergoes thorough quality testing before leaving the factory.



### No sweat.

CORIO™ works robust and reliable – even at ambient temperatures of up to +40 °C.



### Brilliant.

Bright display with strong illumination can be viewed easily from a long distance.



### Quick start.

Individual JULABO consultation and comprehensive manuals at your disposal.



### Cleaning. Easy.

Not only do the new units look good. The functional design makes cleaning a breeze.



### Safety.

CORIO™ CD complies with Class III (FL) according to DIN 12876-1 and switches off automatically in case of high temperature or low liquid level alarm.



### Everything at the front.

All operating controls and safety functions are accessed easily and comfortably from the front.



### Satisfied customers.

11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



### Flexibility.

The jet nozzle permits continuous adjustment of the pump stream in your bath.



### Services 24/7.

Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at [www.julabo.com](http://www.julabo.com).



### Green technology.

Development consistently applied environmentally friendly materials and technologies.



### Soft. Quiet.

CORIO™ circulators are cushion mounted. Protects the electronics. Reduces operating noise and vibration.



### JULABO. Quality.

Highest standards of quality for a long product life.



### Switch on. And off you go.

Intelligent operating concept. Ready for operation with just a few quick and easy steps.



### Locked in.

The lockable power plug guarantees safe connection. More process safety.



### Universal.

Universal bath attachment clamp. For straight containers. For round containers. For laboratory stands.

**JULABO Contact**

JULABO GmbH  
Gerhard-Juchheim-Strasse 1  
77960 Seelbach / Germany

Tel. +49 (0) 7823 51-0  
[info.de@julabo.com](mailto:info.de@julabo.com)

**JULABO Services**

Product finder, Accessory search, 1 PLUS Warranty, Catalog download, Callback service, Operating manuals, Safety data sheets, Software and more

[www.julabo.com](http://www.julabo.com)

Technical changes without prior notification. Images may deviate from the original. For applications near or below ambient temperature: use a cooling coil or JULABO immersion cooler.