

Water Baths

Speciality - Circulating



FEATURES

- Easy-to-Clean Stainless Steel Tank
- Pocket Handles for Easy Lifting
- Recessed Heating Element Prevents "Burnout"
- Unique SHEL LAB Design Eliminates "Hot Spots"
- Thermometer Clip Included

SHEL LAB special application water baths boast the same features as our other high-performance models, such as: being highly accurate, easy-to-use, rugged, and safe. SHEL LAB speciality water baths include a polymer coating for quick cleaning.

SHEL LAB was the first to introduce the non-contact recessed heating element design to the analytical research market. This curtails element burnout and eliminates tank hot spots that are chronic challenges for other water baths.

The SHEL LAB digital water baths remain an industry standard for precise control and quality of design. The operator is able to calibrate this bath using the touch pad controls. This is a convenient feature for facilities concerned with IQ/OQ/PQ validation. The SHEL LAB constant temperature digital water baths are perfect for conducting a host of applications including: bacteriological examinations, food processing/QC procedures and microbiology assays.

SHEL LAB digital water baths are durable and dependable.

Water Bath Applications


- Sample Thawing
- Bacteriological Examinations
- Warming Reagents
- Coliform Determinations
- Microbiological Assays



Precise Temperature Control -

- Over Temperature Protection
- Temperature Uniformity $\pm 0.2\%$ at 37°C
- Temperature Range Ambient $+ 5^{\circ}\text{C}$ to 80°C

2 Year
Limited
Warranty!*



Model Number

Speciality Water Baths	110-120V	SWBC22	
	220-230V	SWBC22-2	
	Chambers	Circulating	
Exterior Dimensions (wxdxh)	Inches	15.0 x 25.5 x 9.0	
	cm	38.1 x 64.8 x 22.9	
Bath Tank Dimensions (wxdxh)	Inches	11.5 x 19.5 x 6.2	
	cm	29.2 x 49.5 x 15.8	
Tank Capacity	L	23	
Stainless Steel Gable Cover(s)	Yes/No	Yes - One Included	

*Tank is excluded from the 2 year warranty.

Specifications are based on nominal values at an ambient temperature of 25°C and a line voltage of 120V or 240V respectively. The temperature data is determined in accordance with DIN 12880. We reserve the right to alter technical specifications at any time.

For a complete list of product specifications, call (800)322-4897 or visit the SHELL LAB website, www.shellab.com

0740534 11/17

Distributed by:

NELSON JAMESON

INC.

800-826-8302 nelsonjameson.com